

10.910 | Carbon Fibre Pearl White Total Wrap | Carbon Fibre

Features

This quality multi-layered cast film 10.910 | Carbon Fibre Pearl White has a carbon fibre embossed pattern. It will conform around compound curves, rivets, corrugations and can be applied on to textured surfaces. Our film is ideal for automotive applications covering, wing mirrors, wheel arches, dashboards and bumpers. The vinyl can also be used for general graphics & striping for vehicle bonnets, roofs and boots. The 135 micron product has enough flexibility and conformability for full vehicle wraps and other long term outdoor applications.

Technical & Performance Information

Film Thickness	135 microns
Adhesive Thickness	25 microns
Total Thickness	160 microns
Adhesive Type	Permanent clear solvent based acrylic
Release Liner	130 gsm PE coated krafty liner
Artificial Weathering *	> 5 years
Film Tensile Strength MD	-
Film Elongation MD	> 100%
Adhesion to steel (20 mins / 180°)	11N /25mm
Adhesion to steel (24 hrs / 180°)	16N /25mm
Dimensional Stability	<0.2%
Application Temperature	+5 to +40°C
Service Temperature	-45 to +115°C

* equivalent to vertical exposure in Mid-European climate

Groendreef 35
B-9880 Aalst | Belgium
T +32 9 216 6700
F +32 9 216 6709
W www.isee2.eu

Warranty

iSee2 warrants our material for one (1) year from date of shipment. The shelf life of our material is dependent on storage conditions. We recommend that the end user stores the material in the original boxes (out of direct sunlight) from our factory. We also recommend to store our material at 21°C with 50% relative humidity. iSee2 only warrants our products to be free from defects in workmanship or defects in iSee2 material. We will replace or credit any material deemed defective. No acceptance or responsibility for loss, damage or expense implied or otherwise shall be assumed by the seller or manufacturer. User assumes all risk and liability in connection herewith. All data values quoted above are typical and should not be used to deem the product defective, if not measured values are different